

Manual phoropter



Specification

Sphere power range	: +26.75D to -29.00 (When optical ± 10.00 D lens is in use) +16.75D, with minimum reading 0.25D or 0.12D (When +0.12 Auxiliary lens or Optical ± 0.12 D lens is in use)
Cylinder power range	: 0 to -6.00D, With minimum reading 0.25D or 0.12D (When auxiliary lens is in use) 0 to -8.00D (When -2.00D auxiliary is use)
Astigmatic axis cable	: 0 to 1800 in 50 Step
Material	: Metal
Dimensions	: 500(w) x 500 (D) x 570 (H)
Weight	: 29kg